












# Typical ADA Railing Installation

## Components:

- 1** 104" Grab Rail with aluminum insert  
1.5" OD x 104"  

ADA104W  
ADA104B
- 2** Aluminum Joiner Kit  
1" OD x 6"  

ADAJKT
- 3** 4" x 4" 90° Inside/Outside Corner  
1-1/2" OD x 4" x 4"  

ADAOSCW  
ADAOSCB
- 4** Inline Wall Mount Bracket  
3"  

ADAIWBW  
ADAIWBB
- 5** Inside Corner 90° Standoff Bracket  
6-1/4"  

ADAINCW  
ADAINCB
- 6** End Cap  
1-1/2"  

ADAECAPW  
ADAECAPB
- 7** Handicap Loop  
18" x 12" x 18"  

ADAHDLW  
ADAHDLB
- 8** Adjustable Internal Joiner  

ADAADJ
- 9** 90° Return Bracket  
3.75" x 3.5"  

ADA90RBW  
ADA90RBB
- 10** External Swivel Connector  

ADAEXTW  
ADAEXTB
- 11** Standoff Bracket  
2-1/4"  

ADASOBW  
ADASOBB

